



BREAKER 40A 2P 120/240V 10K BLE GFI 30MA

General technical data	
number of poles	2
suitability for operation	Electrical Distribution
Electricity	
continuous current rated value	40 A
Model	
product brand name	SIEMENS
type of electrical connection	BOLT-ON
Mechanical Design	
depth [in]	6 in
design of the product	BL
height [in]	3 in
width [in]	3 in
General product approval	
standard	UL 489

last modified: 1/7/2021 

