











Breaker BQD 2P 60A 347/600VAC 10kA CSA

General technical data	
number of poles	2
suitability for operation	CONSTRUCTION
Electricity	
continuous current rated value	60 A
supply voltage frequency rated value 50/60 Hz	Yes
Environmental conditions	
ambient temperature during operation maximum	40 °C
Model	
product brand name	SIEMENS
special product feature	PANELBOARD MOUNT
type of electrical connection	LOW TAB
Mechanical Design	
depth [in]	4 in
design of the overload release	THERMAL MAGNETIC TRIP UNIT
design of the product	BQD
height [in]	2 in
material of the enclosure	MOLDED CASE CIRCUIT BREAKER
size of the circuit-breaker	100A
width [in]	3 in
General product approval	
standard	UL 489 CSA-C22.2
General Product Approval	
Confirmation	KC
	
	Special Test Certificate
Test Certificates	
Marine / Shipping	
Type Test Certificates/Test Report	    
Marine / Shipping	
other	
	Confirmation
Household and similar appliances	
Railway	
Vibration and Shock	Confirmation
Environment	
Environmental Confirmations	

last modified:

12/21/2020 

