

Project Name

Location

Prepared By



SATCO S23143

80W/LED/CCT/100-277V/EX39

Notes

[www] 10-22-2023 23:52:09

General

Status	Active
Watts	80W/63W/54W
Incandescent Equivalent	150W-250W
HID Equivalent	320W/250W/200W
Volts	100V-277V
Shape	Corncob
Base	Mogul Extended
ANSI Base	EX39
Finish	White
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Warm to Cool White
CRI	80
Lumens	11200L/8820L/7560L
Beam Spread	300
Hours Rated	50000
Lamp Type	Corncob
Technology	LED
Min Compartment Size	Length: 9.85 in. Width: 9.85 in. Height: 10.95 in.
Ballasting Requirements	Ballast Bypass

Electrical

Operating Frequency	50-60Hz
Power Factor	>0.9
Operating Position	Base Up or Down
Surge Protection	Built-in surge protection - 4KV
THD	12.30%
Operating Temperature	-40C (-40F) to +60C (+140F)

Physical

MOL	9.96
MOD	5.11
Lens Material	Plastic
Housing Color	Dark Gray
Weight (lb.)	2.68

Additional Information

Additional Info	Power selectable
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	S-7YQW1Z
CA T20 / T24 Rationale	Exempt - Base Not Regulated
NSF Approved	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
<http://www.satco.com/>

