

Project Name

Location

Prepared By



## SATCO S23140

45W/LED/CCT/100-277V/E26

### Notes

[www] 10-22-2023 23:52:09

### General

Status	Active
Watts	45W/36W/27W
Incandescent Equivalent	125W
HID Equivalent	175W/150W/125W
Volts	100V-277V
Shape	Corncob
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Warm to Cool White
CRI	80
Lumens	6300L/5040L/3780L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Corncob
Technology	LED
Ballasting Requirements	Ballast Bypass

### Electrical

Operating Frequency	50-60Hz
Dimming Note	Dimmable only via the wattage/lumen selectable dial included on lamp
Power Factor	>0.9
Operating Position	Universal
Surge Protection	Built-in surge protection - 4KV
Operating Temperature	-40C (-40F) to +60C (+140F)

### Physical

MOL	9.45
MOD	3.35
Lens Material	Plastic
Housing Color	Dark Gray
Weight (lb.)	1.63

### Additional Information

Additional Info	Power selectable
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - Hi-Pro

### Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	No
CA T20 / T24 Rationale	Exempt - >2600 Lumens
NSF Approved	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes

Copyright 2020 Satco Products, Inc.  
All Rights Reserved

For More Information Visit:  
<http://www.satco.com/>

