

Project Name

Location

Prepared By



## SATCO S9490

6.5MR16/LED/25/27K/12V

### Notes

[www] 05-15-2023 01:50:14

### General

Status	Active
Watts	6.5W
Incandescent Equivalent	50W
Volts	12V
Shape	MR16
Base	Bi Pin GU5.3
ANSI Base	GU5.3
Finish	Gray
CCT (Kelvin)	2700K
Temperature	Warm White
CRI	80
Lumens	500L
Beam Spread	25
Dimmable	Yes-Dimmable
Dimming Note	Check the transformer/driver MFG for dimmer compatibility
Hours Rated	25000
Lamp Type	MR
Technology	LED

### Electrical

CBCP	2325
Candlepower	2325
Power Factor	0.93
Operating Temperature	-25C (-13F) to +45C (+113F)

### Physical

MOL	1.772
MOD	1.969
Lensed	Lensed Lamp
Lens Finish	Clear
Housing Color	Gray
Weight (lb.)	0.08

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

### Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2278518
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Washington Status	Lawful for sale
Vermont Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes

Copyright 2020 Satco Products, Inc.  
All Rights Reserved

For More Information Visit:  
<http://www.satco.com/>

