

Project Name

Location

Prepared By



# SATCO S39914

14T8/LED/48-835/BP/SE-DE

## Notes

[www] 05-22-2023 14:10:16

### General

Status	Active
Watts	14W
Fluorescent Equivalent	32W
Volts	120V-277V
Ballast Type	Type B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48.00
Finish	Gloss White
CCT (Kelvin)	3500K
Temperature	Neutral White
CRI	82
Lumens	1700L
Beam Spread	210
Hours Rated	50000
Lamp Type	T8
Technology	LED

### Electrical

Ballasting Requirements	Ballast Bypass
Operating Frequency	50/60Hz
Power Factor	0.9
THD	20%
Operating Temperature	-20C (-4F) to +45C (+113F)

### Physical

MOL	47.78
MOD	1.1
Material	Glass
Lens Finish	Gloss White
Lens Material	Glass
Housing Color	White
Weight (lb.)	0.44

### Additional Information

Additional Info	Equivalent CCT selectable option available in S11766
Tube Guard Use	Approved for use with tube guards
Specification Note	Built-in shock resistant circuit - (not hot until both ends are installed)
Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass

### Compliance

Safety Listing	cULus - Classified; cRUus - Recognized Component
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLU16YJKF707
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California

Title 20 / 24 Status	Lawful for sale
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Washington Status	Lawful for sale
Vermont Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc.  
All Rights Reserved

For More Information Visit:  
<http://www.satco.com/>

