

Project Name

Location

Prepared By



SATCO S11581

5.5PAR20/LED/5CCT/FL/120V

Notes

[www] 11-01-2023 00:12:53

General

| | |
|-------------------------|-------------------------------|
| Status | Active |
| Watts | 5.5W |
| Incandescent Equivalent | 50W |
| Fluorescent Equivalent | 11W |
| Volts | 120V |
| Shape | PAR20 |
| Base | Medium |
| ANSI Base | E26 |
| Finish | Silver |
| CCT (Kelvin) | 2700K/3000K/3500K/4000K/5000K |
| Temperature | Warm White to Natural Light |
| CRI | 90 |
| Lumens | 500L |
| Beam Spread | 40 |
| Dimmable | Yes-Dimmable |
| Hours Rated | 25000 |
| Lamp Type | PAR |
| Technology | LED |

Electrical

| | |
|-----------------------|----------------------------|
| Operating Frequency | 60Hz |
| CBCP | 884 |
| Spot Type | FL - Flood |
| Power Factor | 0.7 |
| Operating Temperature | -20C (-4F) to +40C (+104F) |

Physical

| | |
|---------------|--------------------|
| MOL | 3.19 |
| MOD | 2.48 |
| Lensed | Lensed Lamp |
| Lens Finish | Clear |
| Lens Material | Polycarbonate (PC) |
| Housing Color | Silver |
| Weight (lb.) | 0.1 |

Additional Information

| | |
|----------------------------|--------------------------------|
| Rated For Enclosed Fixture | Yes |
| Warranty | 3 Year Limited - 12 hr per day |

Compliance

| | |
|------------------------|-------------------------------|
| Safety Listing | cULus - Listed |
| Location Rating | Wet |
| CA T20 / T24 Rationale | T20 Listed |
| California Status | Lawful for sale in California |
| Title 20 / 24 Status | Lawful for sale |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |
| SDS Sheet | LED_Lamp |

