SK CEILING FAN HEATER







HEAT FROM ABOVE

The SK ceiling fan heater silently beams down heat from above. This unique model is ideal for rooms where wall space is limited. In bathrooms, the SK can be installed just outside the shower or bathtub. With its ceiling-recessed casing, the SK is an excellent way to provide discreet air circulation. The result: uniform heating and air movement, and reduction in mirror and window fog. By adding a wall timer, you can use it on demand.

- CEILING MOUNTED
 IDEAL FOR ROOMS WITH LIMITED WALL SPACE
- HEATING ON DEMAND OPTIONAL WALL TIMER
- COMPACT AND QUIET
- 347 V MODEL AVAILABLE

COLOURS

- · standard: white, soft white
- Orora (optional): refer to www.stelpro.com/en-CA/Orora)

FINISH

• epoxy-polyester powdercoat

MANUFACTURING

- 22-gauge steel cabinet and 1/4 in. (6.4 mm) deep 20-gauge steel front grille
- easy access for maintenance (no screws)

THERMAL PROTECTION

• thermal protection with automatic reset

ELEMENT

• nichrome element produces instant heat

CONTROL

- built-in thermostat (optional)
- wall thermostat (not included) the use of an electronic thermostat is strongly recommended
- 60 minute timer (optional)

INSTALLATION

- ceiling mounted (recommended height 8 ft., maximum 9 ft.)
- surface mounted with surface adapter (optional)
- recessed or surface mounted with adapter for suspended ceiling (optional)
- unit can be mounted parallel or perpendicular to ceiling beams
- approved to be recessed in mineral wool; for all other materials please check with insulating product manufacturer

WARRANTY

five years

IDFAL FOR

bathroom, entryway, daycare centre, room with limited wall space






| | | ΓΕCHNICAL | SPEC | IFICAT | IONS | 3 | | | | | |
|--------------------|------------------------|--------------|-----------|---------|------|-------------------|-------|-----------|----|--------|----|
| WITHOUT CONTROL | BUILT-IN THERMOSTAT | 24 V CONTROL | POWER | VOLTAGE | FLOW | THROW DISTANCE | | HEAT RISE | | WEIGHT | |
| CODE | CODE | CODE | WATTS | VOLTS | CFM | М | FT. | °C | °F | KG | LB |
| SK0501 | | | 500 | 120 | 60 | 2.4 | 8 | 15 | 26 | 5 | 11 |
| SK0508 | | | 500 | 208 | 60 | 2.4 | 8 | 15 | 26 | 5 | 11 |
| SK0502 | | | 500/375 | 240/208 | 60 | 2.4 | 8 | 15 | 26 | 5 | 11 |
| SK0503 | SK0503T | SK0503C24 | 500 | 347 | 60 | 2.4 | 8 | 15 | 26 | 5 | 11 |
| SK0751 | | | 750 | 120 | 60 | 2.4 | 8 | 22 | 39 | 5 | 11 |
| SK0758 | | | 750 | 208 | 60 | 2.4 | 8 | 22 | 39 | 5 | 11 |
| SK0752 | | | 750/560 | 240/208 | 60 | 2.4 | 8 | 22 | 39 | 5 | 11 |
| SK0753 | SK0753T | SK0753C24 | 750 | 347 | 60 | 2.4 | 8 | 22 | 39 | 5 | 11 |
| SK1001 | | | 1000 | 120 | 60 | 2.4 | 8 | 29 | 53 | 5 | 11 |
| SK1008 | | | 1000 | 208 | 60 | 2.4 | 8 | 29 | 53 | 5 | 11 |
| SK1002 | | | 1000/750 | 240/208 | 60 | 2.4 | 8 | 29 | 53 | 5 | 11 |
| SK1003 | SK1003T | SK1003C24 | 1000 | 347 | 60 | 2.4 | 8 | 29 | 53 | 5 | 11 |
| SK1251 | | | 1250 | 120 | 60 | 2.4 | 8 | 37 | 66 | 5 | 11 |
| SK1258 | | | 1250 | 208 | 60 | 2.4 | 8 | 37 | 66 | 5 | 11 |
| SK1252 | | | 1250/940 | 240/208 | 60 | 2.4 | 8 | 37 | 66 | 5 | 11 |
| SK1253 | SK1253T | SK1253C24 | 1250 | 347 | 60 | 2.4 | 8 | 37 | 66 | 5 | 11 |
| SK1501 | | | 1500 | 120 | 60 | 2.4 | 8 | 44 | 79 | 5 | 11 |
| SK1508 | | | 1500 | 208 | 60 | 2.4 | 8 | 44 | 79 | 5 | 11 |
| SK1502 | | | 1500/1125 | 240/208 | 60 | 2.4 | 8 | 44 | 79 | 5 | 11 |
| SK1503 | SK1503T | SK1503C24 | 1500 | 347 | 60 | 2.4 | 8 | 44 | 79 | 5 | 11 |
| | | | 2000 | 120 | 90 | 3.2 | 10'6" | 39 | 70 | 5 | 11 |
| | | | 2000 | 208 | 90 | 3.2 | 10'6" | 39 | 70 | 5 | 11 |
| SK2002 | | | 2000/1500 | 240/208 | 90 | 3.2 | 10'6" | 39 | 70 | 5 | 11 |
| SK2003 | SK2003T | SK2003C24 | 2000 | 347 | 90 | 3.2 | 10'6" | 39 | 70 | 5 | 11 |


Add W for white or SW for soft white (consult the optional colours chart or contact your Stelpro representative for all other colours). Models also available in 277 V.

⁻⁻⁻ not available

| | ACCESSORIES |
|-----------|---|
| PRODUCT | DESCRIPTION |
| SKT1* | tamper-proof built-in thermostat [120 V-347 V] (grille must be removed to access this type of thermostat) |
| SKTBA* | adapter for suspended ceiling (2 ft. x 2 ft.) – recessed or surface mounted with surface adapter (not included) |
| SKSA* | surface adapter (SK model) |
| FD60MCW70 | 60 minute wall timer [120 V-277 V] |
| SKRE153T* | built-in electronic low voltage relay c/w transformer 24 V [15 A @ 208 V-347 V] |

^{*} Add W for white or SW for soft white. * Factory installed





Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-colour products. For all the latest models and prices, please refer to our website at www.stelpro.com.