

Project Name

Location

Prepared By



## SATCO S11590

13.3PAR38/LED/5CCT/WFL/120V

### Notes

[www] 11-01-2023 00:12:53

### General

Status	Active
Watts	13.3W
Incandescent Equivalent	90W
Fluorescent Equivalent	23W
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	Silver
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Temperature	Warm White to Natural Light
CRI	90
Lumens	1200L
Beam Spread	60
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

### Electrical

Operating Frequency	60Hz
CBCP	1000
Spot Type	WFL - Wide Flood
Power Factor	0.7
Operating Temperature	-20C (-4F) to +40C (+104F)

### Physical

MOL	5.12
MOD	4.76
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
Housing Color	Silver
Weight (lb.)	0.34

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 12 hr per day

### Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

