

Project Name

Location

Prepared By



NUVO 65-881

LED SMALL EM WALL PACK BLACK

Notes

[www] 11-01-2020 00:12:50

General

Status	Active
Fixture Type	Wall Pack
Finish	Black
Wattage	15W
Lumen Output	1740L-1814L
CCT (Kelvin)	3500K/4000K/5000K
IP Rating	IP65
Indoor or Outdoor Fixture	Indoor; Outdoor

Specifications

Technology	LED
CRI	80
Voltage	120V-277V
Beam Angle	100
Rated Hours	50000
Operating Temperature	0C (+32F) to +45C (+113F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming
Photocell or Sensor	Has Photocell
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 2.5KV
Weight (lb.)	3.61
Material	Die-cast Aluminum

Dimensions

Height (in.)	10.47
Width (in.)	6.54
Extension (in.)	3.78

Compliance

Safety Listing	cULus
Location Rating	Wet
DLC Approved	Yes
DLC ID	S-FW6VDL
B.U.G. Rating	B1-U3-G1
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Flicker Free	No
SDS Sheet	LED_Fixture

Additional Information

Additional Information	Battery Mode: 5 Watts, 90 Minute Run Time
Warranty	5 Year Limited - Fixtures

