

Project Name

Location

Prepared By



## SATCO S11777

14A19/LED/3CCT/E26/120V/4PK

### Notes

[www] 11-01-2020 00:12:54

### General

|                         |                             |
|-------------------------|-----------------------------|
| Status                  | Active                      |
| Watts                   | 14W                         |
| Incandescent Equivalent | 100W                        |
| Volts                   | 120V                        |
| Shape                   | A19                         |
| Base                    | Medium                      |
| ANSI Base               | E26                         |
| Finish                  | White                       |
| CCT (Kelvin)            | 3000K/4000K/5000K           |
| Temperature             | Warm White to Natural Light |
| CRI                     | 90                          |
| Lumens                  | 1500L                       |
| Beam Spread             | 220                         |
| Dimmable                | Non-Dimmable                |
| Hours Rated             | 10000                       |
| Lamp Type               | Type A                      |
| Technology              | LED                         |

### Electrical

|                       |                            |
|-----------------------|----------------------------|
| Operating Frequency   | 60Hz                       |
| Power Factor          | 0.7                        |
| Operating Temperature | -20C (-4F) to +45C (+113F) |

### Physical

|               |       |
|---------------|-------|
| MOL           | 4.59  |
| MOD           | 2.36  |
| Housing Color | White |
| Weight (lb.)  | 0.13  |

### Additional Information

|                            |                |
|----------------------------|----------------|
| Rated For Enclosed Fixture | Yes            |
| Warranty                   | 3 Year Limited |

### Compliance

|                        |                               |
|------------------------|-------------------------------|
| Safety Listing         | cULus - Listed                |
| Location Rating        | Damp                          |
| Energy Star            | No                            |
| CA T20 / T24 Rationale | T20 Listed                    |
| California Status      | Lawful for sale in California |
| Title 20 / 24 Status   | Lawful for sale               |
| RoHS Compliant         | Yes                           |
| SDS Sheet              | LED_Lamp                      |