

Project Name

Location

Prepared By



Notes

[www] 11-01-2023 00:12:53

General

Status	Active
Watts	14W
Incandescent Equivalent	100W
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	90
Lumens	1150L
Beam Spread	40
Dimmable	Non-Dimmable
Hours Rated	15000
Photocell or Sensor	Has PIR Sensor
Lamp Type	PAR
Technology	LED

Electrical

Operating Frequency	60Hz
Power Factor	0.8
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	5.35
MOD	4.85
Weight (lb.)	0.76

Additional Information

The lamp has an integrated motion-activated sensor designed to activate between dusk and dawn. It remains inactive in the absence of motion but turns on for a duration of 5 minutes once motion is detected. This functionality can be overridden by toggling the bulb's switch on and off twice within a span of 3 seconds, allowing it to remain continuously illuminated like a standard light bulb.

Rated For Enclosed Fixture	No
Installation Notes	To achieve optimal sensor reading, make sure the sensor is facing the desired motion area within proper distance and angle.
Specification Note	Dual Mode Capable: Motion or On-Off Switch
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
CA T20 / T24 Rationale	T20 Listed

California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
<http://www.satco.com/>

