

Project Name

Location

Prepared By



# SATCO S22217

11.5PAR38/LED/940/FL/120V

Notes

[www] 05-15-2023 01:50:10

## General

Status	Active
Watts	11.5W
Incandescent Equivalent	90W
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	4000K
Temperature	Cool White
CRI	90
Lumens	1000L
Beam Spread	40
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	PAR
Technology	LED

## Electrical

Operating Frequency	60Hz
Candlepower	90
Power Factor	0.7
Operating Temperature	-20C (-4F) to +45C (+113F)

## Physical

MOL	5.12
MOD	4.76
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Plastic (PS)
Housing Color	White
Weight (lb.)	0.06

## Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

## Compliance

Safety Listing	cULus - Listed
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2382238;2394158
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Washington Status	Lawful for sale
Vermont Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes

