

Project Name

Location

Prepared By



# SATCO S12447

18.5A21/FR/LED/E26/830/120V

**Notes**

[www] 06-15-2022 03:20:43

**General**

Status	Active
Watts	18.5W
Incandescent Equivalent	150W
Volts	120V
Shape	A21
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	3000K
Temperature	Soft White
CRI	80
Lumens	2610L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

**Electrical**

Operating Frequency	60 Hz
Operating Temperature	-20C (-4F) to +45C (+113F)

**Physical**

MOL	5.20
MOD	2.76

**Additional Information**

Rated For Enclosed Fixture	No
Warranty	3 Year Limited

**Compliance**

Safety Listing	cULus - Listed
Location Rating	Wet
Energy Star	No
CA T20 / T24 Rationale	Exempt - >2600 Lumens
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes