

Project Name

Location

Prepared By



## SATCO S13146

30W/LED/UTL/MB/5000K

### Notes

[www] 05-15-2023 01:50:09

### General

Status	Active
Watts	30W
Incandescent Equivalent	200W
Volts	120V
Shape	Multi-Beam
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80
Lumens	3000L
Beam Spread	100-300
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	LED HID
Technology	LED

### Electrical

Operating Frequency	60Hz
Power Factor	0.9
Operating Position	Universal
Operating Temperature	-20C (-4F) to +45C (+113F)

### Physical

MOL	4.50
MOD	13.98
Lens Material	Plastic (PS)
Housing Color	White
Weight (lb.)	1.05

### Additional Information

Rated For Enclosed Fixture	No
Warranty	5 Year Limited - 10 hr per day

### Compliance

Safety Listing	cETLus - Classified
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2398099
CA T20 / T24 Rationale	Exempt - >2600 Lumens
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp