

Quality Products. Service Excellence.

Type 4X Painted Stainless Steel Wallmount Enclosure Eclipse Series

Hinge Door with Handle













Application

- Designed to enclose electrical and/or electronic equipment and protect against harsh, industrial environments for wallmount applications.
- Impressive styling features like hidden hinges and attractive latching systems make the Eclipse a suitable addition to any high-tech equipment installation.
- A wide range of sizes and practical accessories make this product line a complete package.

Standards

- UL 508A Type 3R, 4, 4X and 12
- CSA Type 3R, 4, 4X and 12
- · Complies with
 - o NEMA 3R, 4, 4X, 12 and 13
 - o IEC 60529, IP 66

Construction

- · Formed 304 stainless steel.
- Continuously welded seams ground smooth.
- Door stiffeners are provided where required for increased strength and rigidity designed to also permit additional mounting options.
- Formed lip on enclosure to exclude flowing liquids and contaminants.
- Doors are secured with a 3 point Handle in 316 stainless with pad lockable feature.
- Doors may be easily removed for modifications and are interchangeable.
- · Seamless poured-in place gasket.
- Collar studs provided for mounting inner panel.
- Includes hardware kit with panel mounting nuts and sealing washers for wall mounting holes.
- Bonding stud provided on door and grounding stud installed in enclosure.
- Stainless steel hinge pins and hinges.

Finish

 Cover and enclosure are finished in recoatable smooth RAL 9003 White powder coating inside and out.


Accessories


- Cooling Products
- Ventilation
- DIN Rail Mounting Kit
- Drip Shield Kit
- Heaters
- Inner Panels
- Literature Pocket
- Padlock Adaptor


- Blowers and Fans
- DIN Rails
- Door Stop Kit
- Filtered Fans
- Handles
- Quarter Turn Inserts and Keys
- Mounting Foot Kit
- Swing Panel

- Swing Frame
- Replacement Hinge Pins
- Quarter Turn Assemblies
- Type 4 Hardware Kits

- Rear Hole Plugs
- Temperature Controls
- Touch-Up Spray Paint
- Ground Wire Kits







| Part No. | Overall Dimensions | | | Door/Body | Optional Panel | Panel Size | | Hinges | Ship Wt. |
|-----------------|--------------------|-------|-------|-----------|----------------|------------|-------|--------|----------|
| | Α | В | С | Gauge | Part No. | E | F | | Lbs. |
| EN4SD24248SSWH | 24.00 | 24.00 | 8.00 | 14 | EP2424 | 22.20 | 22.20 | 2 | 32 |
| EN4SD30248SSWH | 30.00 | 24.00 | 8.00 | 14 | EP3024 | 28.20 | 22.20 | 3 | 46 |
| EN4SD242010SSWH | 24.00 | 20.00 | 10.00 | 14 | EP2420 | 22.20 | 18.20 | 2 | 38 |
| EN4SD242412SSWH | 24.00 | 24.00 | 12.00 | 14 | EP2424 | 22.20 | 22.20 | 2 | 47 |
| EN4SD363012SSWH | 36.00 | 30.00 | 12.00 | 14 | EP3630 | 34.20 | 28.20 | 3 | 99 |
| EN4SD363612SSWH | 36.00 | 36.00 | 12.00 | 14 | EP3636 | 34.20 | 34.20 | 3 | 104 |
| EN4SD423612SSWH | 42.00 | 36.00 | 12.00 | 14 | EP4236 | 40.20 | 34.20 | 4 | 109 |
| EN4SD483612SSWH | 48.00 | 36.00 | 12.00 | 14 | EP4836 | 46.20 | 34.20 | 4 | 124 |
| EN4SD483616SSWH | 48.00 | 36.00 | 16.00 | 14 | EP4836 | 46.20 | 34.20 | 4 | 135 |
| EN4SD603612SSWH | 60.00 | 36.00 | 12.00 | 14 | EP6036 | 58.20 | 34.20 | 4 | 155 |

Data subject to change without notice

© 2017. Hammond Manufacturing Ltd. All rights reserved.