Vertical Rack Cable Manager with Door RB-VCM Series



HAMMOND MANUFACTURING.







Vertical cable managers facilitate cable organization for a single or multiple rack installation. The RB-VCM44 is cost-effective and includes a number of unique features to save you installation time.

Features

- Manager body and door are constructed of 16-gauge steel.
- All-steel construction with side and rear cut-outs for cable pass-through.
- Includes cable mounting lances for hook and loop cable organization.
- Mounts to either side of open frame rack (includes mounting hardware).
- Attached hinged door opens to one side and secures closed with two (2) small strips of magnet.
- Horizontal stabilizers easily swing away for cable installation and swing back for structural support.
- Separated space easily allows for cables to be added or removed without fishing the cable.
- Manager and door finished in textured black power coat finish.
- RoHS Compliant.
- Manufactured in North America.

Compatibility

- Designed specifically for the RB-2P77 and RB-2PA45 but also compatible with:
- DRZ477
- DNRR**HDW Series
- DC2R44
- DC4R Series
- **RRAL Series**

Part of the Rack Basics® line of economy rack solutions.

Accessories

• Top Cable Chimney

• Hook and Loop Roll

	Overall D	imensions	(Inches)	Mounti	Door	
Part No.	Height	Width	Depth	Units	Rack Units	Included
RB-VCM44	82.00	6.00	5.00	77.00	44	Yes
RB-VCM48	89.00	6.00	5.00	85.00	48	Yes

Estimated Cable Fill Capacities

Part		Opening	Recommended Cable Fill (50% Fill Ratio)			Maximum Cable Fill (100% Fill Ratio)		
No.	Description	Quantity	Cat 5e	Cat 6	Cat 6a	Cat 5e	Cat 6	Cat 6a
RB- VCM44	Channel Opening	1	271	173	120	541	346	241
	Side Opening	2 x 16 = 32	56	36	25	113	72	50
	Rear Pass Through	8	25	16	11	49	32	22

Data subject to change without notice

© 2017. Hammond Manufacturing Ltd. All rights reserved.