


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE		PACKAGE QTY. (PER STRIP)	COLOR (DIN)	MAX. WIRE INSULATION DIAMETER	WIRE CLASS	DIMENSIONS in. [mm ²]				INSTALLATION TOOL
	AWG	[mm ²]					L	P	OD (REF.)	ID	
* FSD75-8-DSL10	22-20	[0,50]	500 (50)	WHITE	0.10 [2,6]	B, K, M	0.60 [15,2]	0.31 [8,0]	0.05 [1,4]	0.04 [1,0]	CT-1000
FSD76-8-DSL8	18	[0,75]	500 (50)	GRAY	0.11 [2,7]	B, K, M	0.60 [15,2]	0.31 [8,0]	0.06 [1,6]	0.05 [1,2]	
FSD77-8-DSL2	-	[1,00]	500 (50)	RED	0.12 [3,0]	B, K, M	0.60 [15,2]	0.31 [8,0]	0.07 [1,8]	0.06 [1,5]	
FSD78-8-DSL0	16	[1,50]	500 (50)	BLACK	0.13 [3,2]	B, K, M	0.60 [15,2]	0.31 [8,0]	0.08 [2,1]	0.07 [1,8]	
FSD80-8-DSL6	14	[2,50]	500 (50)	BLUE	0.16 [4,0]	M	0.60 [15,2]	0.31 [8,0]	0.10 [2,6]	0.09 [2,3]	



* UL LISTED WITH 20AWG ONLY, UL486F SCOPE IS 20 - 1/0 AWG ONLY. WHITE IS DIN COLOR FOR 20AWG [0,5]

NOTES:

1. USED FOR:


- A. UL LISTED WITH STRANDED COPPER WIRE ONLY
- B. 221°F [105°C] MAX. OPERATING TEMPERATURE

2. WIRE STRIP LENGTH: 13/32" ^{+1/32}₋₀ [10,0^{+0,8}₀]

3. MATERIAL:

- A. STAMPING: COPPER, TIN PLATED
- B. HOUSING: POLYPROPYLENE, COLOR CODED
- C. COLOR CODE CONFORMS TO DIN 46228 STANDARD

4. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



PART NUMBER		SEE TABLE		
TITLE		FERRULES WITH SLEEVES ON CONTINUOUS REEL (DIN)		
ITEM REVISION NAME		CUSTOMER DRAWING		
DATASET FILE NAME		N41736BA/09		
MATERIAL		N41736BA_DC/09A		
DRAWING NUMBER		A41736		
DRAWN BY		DAW		
DATE		01-07		
CHK		-		
SCALE		N.T.S		
SHEET 1 OF 1		A		

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
09A	08-21-23	DPOI	JBN	MRWA ASY	ADDED UL ENHANCED MARK - US, CA & UPDATE BORDER.	128785/01

A-SIZE CUSTOMER