

# PHILIPS

# Lighting



## MR16

### 20MR16/FL36 BAB 50PK

Philips Halogen MR16 lamps provide a bright white light for accent lighting. They make it easy to optimize the look and feel of your brand, your merchandise, and the shoppers experience, with lower operating costs.

#### Product data

General information	
Cap-Base	GU5.3 [ GU5.3]
Philips Code	14592
Operating Position	UNIVERSAL [ Any or Universal (U)]
ANSI Code Halogen	BAB
Nominal Lifetime (Nom)	3000 h
Rated Lifetime (Hours)	3000 h
Rated Lifetime (Years)	3 a
Light technical	
Beam Angle (Nom)	36 °
Luminous Intensity (Max)	550 cd
Rated Beam Angle	36 °
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	100
Operating and electrical	
Power (Nom)	20.0 W
Lamp Current (Nom)	1.67 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V

Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Shape	MR16 [ 2inch/50mm]
Luminaire design requirements	
Bulb Temperature (Max)	250 °C
Cap-Base Temperature (Max)	350 °C
Cap-Base Temperature (Max)-DUP(do not use)	662 °F
Product data	
Order product name	20MR16/FL36 BAB 50PK
EAN/UPC - Product	046677378035
Order code	924047217122
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	924047217122
Net Weight (Piece)	0.032 kg
ILCOS Code	HRGI-20-12-GU5.3-50/36

## MR16

### Dimensional drawing



20MR16/FL36 BAB 50PK

Product	D (max)	C (max)
20MR16/FL36 BAB 50PK	51 mm	46 mm

