



Reflector Infrared BR40, PAR38

175PAR38/HEAT/CL 120V 12/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Philips Infrared lamps are suited for heating and drying in industrial and commercial applications. These incandescent, gas-filled infrared heat lamps come up to full temperature almost immediately, eliminating costly warm-up time. Highly efficient heat generators that produce a minimum of light rays and a high amount of infrared radiation. The BR40 lamp provides a built-in reflector for radiant energy control.

Product data

General Information	
Cap-Base	E26/50X39 [Skirted Medium Screw (PAR Lamps)]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	5,000 hour(s)
Rated Lifetime (Hours)	5,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Color Designation	C

Operating and Electrical	
Power Consumption	175 W
Voltage (Nom)	115-125 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]

Product Data	
Full product code	904667711626215
Order product name	175PAR38/HEAT/CL 120V 12/1
Order code	923813534608
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	923813534608
Full product name	175PAR38/HEAT/CL 120V 12/1
EAN/UPC - Case	50046677145519
EAN/UPC - Product/Case	046677116262

Reflector Infrared BR40,PAR38

Dimensional drawing



Product	D	C (max)	C1 (max)
175PAR38/HEAT/CL 120V 12/1	121 mm	135 mm	123 mm

