

Energy Advantage T8

F32T8/ADV830/XEW/ALTO 25W 30PK

Philips Energy Advantage T8 lamps offer high energy savings without sacrificing performance.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	44000 h
Life 12-Hr Instant Start [Hrs]	38000 h
Life 3-Hr Program Start [Hrs]	38000 h
Life 3-Hr Instant Start [Hrs]	32000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	Advantage 830 [CCT of 3000K]
Luminous Flux (Nom)	2500 lm
Color Designation	Advantage 830
Design Mean Lumens	2425 lm
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	85
Operating and Electrical	
Power (Nom)	25 W

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	48
Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	29 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg
Product Data	
Order product name	F32T8/ADV830/XEW/ALTO 25W 30PK
EAN/UPC - Product	046677282042
Order code	927852383103
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927852383103
Net Weight (Piece)	0.136 kg

Warnings and Safety


Datasheet, 2020, May 6 data subject to change

Energy Advantage T8

Dimensional drawing

Product

F32T8/ADV830/XEW/ALTO 25W 30PK



F32T8 25W/831 XEW ALTO ES



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.