



Slimline T12

Slimline F48T12/CW ALTO 15PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Cap-Base	FA8 [FA8]
Life 3-Hr Start [Hrs]	9000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	33
Luminous Flux (Nom)	2950 lm
Color Designation	Cool White (CW)
Design Mean Lumens	2600 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	62
Operating and Electrical	
Power (Nom)	39 W
Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	48
Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	3.5 mg


Product Data	
Order product name	Slimline F48T12/CW ALTO 15PK
EAN/UPC - Product	046677363215
Order code	927890003304
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	927890003304
Net Weight (Piece)	0.001 kg

Slimline T12

Dimensional drawing

Product

Slimline F48T12/CW ALTO 15PK



F48T12 39W/33 ALTO

