



Rapid Start T12

F96T12/DX/HO/ALTO 15PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

General Information		
Cap-Base	R17D [R17d (RDC)]	
Features	ALTO® (ALTO)	
Light Technical		
Color Code	57	
Luminous Flux	6,750 lumen	
Correlated Color Temperature (Nom)	6500 K	
Color rendering index (CRI)	90	
Operating and Electrical		
Power Consumption	110 W	
Mechanical and Housing		
Bulb Shape	T-12 (T12)	

Approval and Application	
Mercury (Hg) Content (Nom)	6.8 mg
Product Data	
Order product name	F96T12/DX/HO/ALTO 15PK
Order code	927894705701
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	927894705701
Full product name	F96T12/DX/HO/ALTO 15PK
EAN/UPC - Case	50046677214895
EAN/UPC - Product/Case	046677214890

Datasheet, 2023, November 6 data subject to change

Rapid Start T12

Dimensional drawing

Product

F96T12/DX/HO/ALTO 15PK



T12 Recessed Double Conta



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.