



Rapid Start T12

F40DX ALTO 30PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)

Light Technical	
Color Code	57
Luminous Flux	2,325 lumen
Color Designation	Daylight Deluxe
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	90

Operating and Electrical	
Power Consumption	40 W

Mechanical and Housing	
Bulb Shape	T-12 (T12)

Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	4.4 mg

Product Data	
Order product name	F40DX ALTO 30PK
Order code	927888005709
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927888005709
Full product name	F40DX ALTO 30PK
EAN/UPC - Case	50046677273595
EAN/UPC - Product/Case	046677273590

Rapid Start T12

Dimensional drawing

Product

F40DX ALTO 30PK

