



T5 High Output

24W/841 Min Bipin T5 HO ALTO UNP

Philips T5 HO lamps are environmentally-responsible, ultra-slim and have extraordinary light output and longer life.

Product data


General Information				
Cap-Base	G5 [G5]			
Features	HO Alto® [High Output Alto]			
Light Technical				
Color Code	841 [CCT of 4100K]			
Luminous Flux	1,950 lumen			
Color Designation	Cool White (CW)			
Correlated Color Temperature (Nom)	4100 K			
Luminous Efficacy (rated) (Nom)	76 lm/W			
Color rendering index (CRI)	82			
Operating and Electrical				
Power Consumption	22.5 W			
Lamp Current (Nom)	0.295 A			
Controls and Dimming				
Dimmable	Yes			

Mechanical and Housing				
Bulb Shape	T5 [16 mm (T5)]			
Approval and Application				
Mercury (Hg) Content (Nom)	1.4 mg			
Product Data				
Order product name	24W/841 Min Bipin T5 HO ALTO UNP			
Order code	927992184022			
Numerator - Quantity Per Pack	1			
Numerator - Packs per outer box	40			
Material Nr. (12NC)	927992184022			
Full product name	24W/841 Min Bipin T5 HO ALTO UNP			
EAN/UPC - Case	50046677290219			
EAN/UPC - Product/Case	046677290214			

Datasheet, 2023, September 22 data subject to change


T5 High Output

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
24W/841 Min Bipin T5 HO ALTO	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
UNP					


Photometric data



Spectral Power Distribution Colour - 24W/841 Min Bipin T5 HO ALTO UNP

Lifetime






Life Expectancy Diagram - 24W/841 Min Bipin T5 HO ALTO UNP

Life Expectancy Diagram - 24W/841 Min Bipin T5 HO ALTO UNP

T5 High Output

Lifetime



Lumen Maintenance Diagram - 24W/841 Min Bipin T5 HO ALTO UNP

