



High Output T12

F72T12/D/HO ALTO 15PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

General Information	
Cap-Base	R17D [R17d (RDC)]
Features	ALTO® (ALTO)
Light Technical	
Color Code	54
Luminous Flux	5,600 lumen
Color Designation	Daylight
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	79
Operating and Electrical	
Power Consumption	85 W
Mechanical and Housing	
Bulb Shape	T-12 (T12)


Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	6.8 mg
Product Data	
Order product name	F72T12/D/HO ALTO 15PK
Order code	927893205402
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	927893205402
Full product name	F72T12/D/HO ALTO 15PK
EAN/UPC - Case	50046677366532
EAN/UPC - Product/Case	046677366537

High Output T12

Dimensional drawing

Product

F72T12/D/HO ALTO 15PK



T12 Recessed Double Contact

