



# High Output T12

## TL F96T12/CW/HO-O ALTO 110W FLUOR. LAMP

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

### Product data

General Information	
Cap-Base	R17D [R17d (RDC)]
Features	ALTO® (ALTO)
Light Technical	
Color Code	33
Luminous Flux	8,800 lumen
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	62
Operating and Electrical	
Power Consumption	110 W
Mechanical and Housing	
Bulb Shape	T-12 (T12)


Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	6.8 mg
Product Data	
Order product name	TL F96T12/CW/HO-O ALTO 110W FLUOR. LAMP
Order code	927895203323
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	927895203323
Full product name	TL F96T12/CW/HO-O ALTO 110W FLUOR. LAMP
EAN/UPC - Case	50046677381764
EAN/UPC - Product/Case	046677381769

# High Output T12

## Dimensional drawing

### Product

TL F96T12/CW/HO-O ALTO 110W FLUOR. LAMP



T12 Recessed Double Contact

