



Sign

BC-25T10/CL

Philips Sign bulbs provide the perfect light for dramatic accents and display lighting that is great for hard to reach signs, indoors and out.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	1,500 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	200 lumen
Operating and Electrical	
Power Consumption	25 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	T-10
Product Data	
Order product name	BC-25T10/CL
Order code	925195136301
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	925195136301
Full product name	BC-25T10/CL
EAN/UPC - Case	50067805125197
EAN/UPC - Product/Case	067805125192

Sign

Dimensional drawing



Product

BC-25T10/CL

