



PL-C Cluster 4-Pin Base

PL-C 13W/835/4P/ALTO 10PK

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.


Product data

General Information	
Cap-Base	G24Q-1 [G24q-1]
Light Technical	
Color Code	835 [CCT of 3500K]
Luminous Flux	925 lumen
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	69 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	13.0 W
Lamp Current (Nom)	0.170 A
Controls and Dimming	
Dimmable	Yes

Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	15 kWh
Product Data	
Order product name	PL-C 13W/835/4P/ALTO 10PK
Order code	927907183530
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927907183530
Full product name	PL-C 13W/835/4P/ALTO 10PK
EAN/UPC - Case	60046677237747
EAN/UPC - Product/Case	046677237745


PL-C Cluster 4-Pin Base

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-C 13W/835/4P/ALTO 10PK	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm

Photometric data




Spectral Power Distribution Colour - PL-C 13W/835/4P/ALTO 10PK

Lifetime



Life Expectancy Diagram - PL-C 13W/835/4P/ALTO 10PK



Life Expectancy Diagram - PL-C 13W/835/4P/ALTO 10PK

PL-C Cluster 4-Pin Base

Lifetime



Lumen Maintenance Diagram - PL-C 13W/835/4P/ALTO 10PK

