



Switch Start Metal Halide Protected

MP400/BU 6 PK

An efficient, protected "O" rated lighting solution that is suitable for open-rated fixtures. Ideal for both indoor and outdoor applications.

Warnings and Safety

• R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data

General Information		
Cap-Base	EX39 [Exclusionary Mogul Screw]	
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]	
Life to 50% Failures (Nom)	20,000 hour(s)	
Light Technical		
Color Code	640 [CCT of 4000K]	
Color Designation	Cool White (CW)	
Chromaticity Coordinate X (Nom)	385	
Chromaticity Coordinate Y (Nom)	390	
Correlated Color Temperature (Nom)	4000 K	
Luminous Efficacy (rated) (Nom)	100 lm/W	
Color rendering index (CRI)	65	
Operating and Electrical		
Lamp Current (Nom)	3.25 A	

Voltage (Nom)	135 V
Voltage (Nom)	135 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED37
Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	57 mg
Product Data	
Order product name	MP400/BU 6 PK
Order code	928601157903
Numerator - Quantity Per Pack	1

Datasheet, 2023, November 6 data subject to change

Switch Start Metal Halide Protected

Numerator - Packs per outer box	6
Material Nr. (12NC)	928601157903
Full product name	MP400/BU 6 PK
EAN/UPC - Case	50046677133325

EAN/UPC - Product/Case	046677133320
	-

Dimensional drawing

Product	D	C (max)
MP400/BU 6 PK	4.625 inch	11.5 inch



