



## **Energy Saver T2**

## EL/mdTQ 13W T2

The Philips EnergySaver T2 provides energy efficient lighting in a smaller, sleeker, size that fits more fixtures. The energy saving T2 is a direct replacement for most incandescents, provides soft white light and lasts 11 years\* reducing the hassle of frequest replacements.


## **Product data**

General Information		
Cap-Base	E26 [Single Contact Medium Screw]	
Nominal lifetime	10,000 hour(s)	
Switching Cycle	5,000	
Rated Lifetime (Hours)	10,000 hour(s)	
Lighting Technology	Compact Fluorescent Integrated	
Light Technical		
Color Code	827 [CCT of 2700K]	
Luminous Flux	900 lumen	
Color Designation	Warm White (WW)	
Chromaticity Coordinate X (Nom)	459	
Chromaticity Coordinate Y (Nom)	412	
Correlated Color Temperature (Nom)	2700 K	
Luminous Efficacy (rated) (Nom)	67 lm/W	
Color rendering index (CRI)	81	
LLMF At End Of Nominal Lifetime (Nom)	50 %	
Operating and Electrical		
Line Frequency	50 or 60 Hz	
Input Frequency	50 or 60 Hz	
Power Consumption	13.0 W	
Lamp Current (Nom)	210 mA	

Power Factor (Fraction)	0.55
Voltage (Nom)	110-127 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	EL/mdTQS
Approval and Application	
Mercury (Hg) Content (Max)	2 mg
Energy Consumption kWh/1000 h	13 kWh
Product Data	
Order product name	EL/mdTQ 13W T2
Order code	929689749502
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929689749502
Full product name	EL/mdTQ 13W T2
EAN/UPC - Case	50046677413991
E411/11D6 D 1 1/6	
EAN/UPC - Product/Case	046677413996

Datasheet, 2023, September 4 data subject to change

## Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/mdTQ 13W T2	51.5 mm	104.3 mm	42.5 mm

