



High Output T8

F48T8/TL841/HO ALTO 25/1

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Cap-Base	R17D [R17d (RDC)]
Features	ALTO® (ALTO)

Light Technical	
Color Code	TL841 [CCT of 4100K (841)]
Luminous Flux	4,000 lumen
Color Designation	TL841
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	86

Operating and Electrical	
Power Consumption	44 W

Mechanical and Housing	
Bulb Shape	T-8 (T8)

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.5 mg

Product Data	
Order product name	F48T8/TL841/HO ALTO 25/1
Order code	927871084104
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927871084104
Full product name	F48T8/TL841/HO ALTO 25/1
EAN/UPC - Case	50046677236798
EAN/UPC - Product/Case	046677236793

High Output T8

Dimensional drawing

Product

F48T8/TL841/HO ALTO 25/1

