

Lighting

PHILIPS

PLUS T8 High Output

F96T8/TL850/PLUS/HO/ALTO 25/1

Philips PLUS T8 High Output 8-foot fluorescent lamps reduce the impact on the environment by offering long life and low mercury.

Product data

General Information	
Cap-Base	R17D [R17d (RDC)]
Features	ALTO® Plus
Light Technical	
Color Code	TL850 [CCT of 5000K (850)]
Luminous Flux	8,100 lumen
Color Designation	TL850
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	86 W
Mechanical and Housing	
Bulb Shape	T-8 (T8)

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F96T8/TL850/PLUS/HO/ALTO 25/1
Order code	927874085005
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927874085005
Full product name	F96T8/TL850/PLUS/HO/ALTO 25/1
EAN/UPC - Case	50046677236897
EAN/UPC - Product/Case	046677236892

PLUS T8 High Output

Dimensional drawing

Product

F96T8/TL850/PLUS/HO/ALTO 25/1





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, November 6 - data subject to change