



High CRI T12

F40T12/CWSupreme/ALTO

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Luminous Flux	2,600 lumen
Color Designation	Cool White Supreme
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	89
Operating and Electrical	
Power Consumption	40 W
Mechanical and Housing	
Bulb Shape	T-12 (T12)

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F40T12/CWSupreme/ALTO
Order code	927887803901
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927887803901
Full product name	F40T12/CWSupreme/ALTO
EAN/UPC - Case	50046677423884
EAN/UPC - Product/Case	046677423889

High CRI T12

Dimensional drawing

Product

F40T12/CWSupreme/ALTO

