



# PL-C Cluster 4-Pin Base

## PL-C 26W/41/4P/ALTO 10PK

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.


### Product data

General Information	
Cap-Base	G24Q-3 [G24q-3]
Light Technical	
Color Code	841 [CCT of 4100K]
Luminous Flux	1,800 lumen
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	67 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	26.0 W
Lamp Current (Nom)	0.335 A
Controls and Dimming	
Dimmable	Yes

Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	29 kWh
Product Data	
Order product name	PL-C 26W/41/4P/ALTO 10PK
Order code	927907384030
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927907384030
Full product name	PL-C 26W/41/4P/ALTO 10PK
EAN/UPC - Case	60046677111771
EAN/UPC - Product/Case	046677111779


# PL-C Cluster 4-Pin Base

## Dimensional drawing





Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-C 26W/41/4P/ALTO 10PK	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm

## Photometric data



Spectral Power Distribution Colour - PL-C 26W/41/4P/ALTO 10PK

## Lifetime



Life Expectancy Diagram - PL-C 26W/41/4P/ALTO 10PK

Life Expectancy Diagram - PL-C 26W/41/4P/ALTO 10PK

## PL-C Cluster 4-Pin Base

### Lifetime



Lumen Maintenance Diagram - PL-C 26W/41/4P/ALTO 10PK

