



# Ceramalux ALTO

## SON 250W E39 ED58 CL SL/12

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

### Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Light Technical	
Chromaticity Coordinate X (Nom)	523
Chromaticity Coordinate Y (Nom)	412
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	102 lm/W
Luminous Efficacy (rated) (Nom)	114 lm/W
Color rendering index (CRI)	26
Operating and Electrical	
Power Consumption	251 W
Lamp Current (Nom)	3.0 A
Voltage (Nom)	95 V
Voltage (Nom)	95 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED18
Approval and Application	
Mercury (Hg) Content (Max)	23.5 mg
Product Data	
Order product name	SON 250W E39 ED58 CL SL/12
Order code	928601139490
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928601139490
Full product name	SON 250W E39 ED58 CL SL/12
EAN/UPC - Case	50046677467215
EAN/UPC - Product/Case	046677467210

# Ceramalux ALTO

## Dimensional drawing

Product	D	C (max)
SON 250W E39 ED58 CL SL/12	57.2 mm	248 mm

