



T8 High CRI Lamps

F32T8/TL941/ALTO 30PK

Philips T8 High CRI lamps featuring ALTO II technology are ideal when better color rendering properties are preferred.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	940 [CCT of 4000K]
Beam Angle (Nom)	0 degree(s)
Luminous Flux	2,600 lumen
Color Designation	4100 Kelvin
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	>90
Operating and Electrical	
Power Consumption	32 W
Lamp Current (Nom)	265 mA
Wattage Equivalent	32 W
Voltage (Nom)	137 V
Voltage (Nom)	137 V

Mechanical and Housing	
Bulb Finish	Coated glass
Bulb Shape	T-8 (T8)
Approval and Application	
Mercury (Hg) Content (Nom)	1.7 mg
Product Data	
Order product name	F32T8/TL941/ALTO 30PK
Order code	927871203901
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927871203901
Full product name	F32T8/TL941/ALTO 30PK
EAN/UPC - Case	50046677479621
EAN/UPC - Product/Case	046677479626

T8 High CRI Lamps

Dimensional drawing

Product	C (max)	D (max)
F32T8/TL941/ALTO 30PK	1,213.6 mm	27.9 mm

