



Optanium T8 Instant Start

OPTANIUM ELE BALLAST (2) F32T8 347V

Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology.

Product data

General Information				
Lamp Type	F32T8			
Number of Lamps	1-2 piece/unit			
Ballast Type	Electronic Fluorescent			
Base Model	GOPA2P32SC			
Suitable For Outdoor Use	Yes			
Automatic Restart	Yes			
Operating and Electrical				
Input Voltage	347 V			
Input Frequency	50 to 60 Hz			
Total Harmonic Distortion USA	10 %			
Ignition Method	Instant Start			
Crestfactor (Nom)	1.6			
Ignition Time (Nom)	0.1 s			
Ballast Factor (Nom)	0.88			
Power Factor (Nom)	0.98			
Input Current (Nom)	0.16 A			
Input Power (Nom)	55 W			
Rated Lamp Power	32 W			

Wiring	
Color Input Terminals	No terminals
Color Output Terminals	No terminals
Wire Striplength	0.375 mm
Lamp Connection	Parallel
Wire Length by Color	See data sheet
Wire Gauge (Nom)	18AWG mm
Wire Type	Solid
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	Yes
Through Wiring Configuration Allowed	Yes
Connector Type	No connector
Temperature	
T-Case Maximum (Nom)	70 °C
Mechanical and Housing	
Housing Material	Metal
Housing	N
Housing Dimensions	9.5" x 1.3" x 1.0"


Datasheet, 2019, March 22 data subject to change

Optanium T8 Instant Start

Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approval Marks	CSA certificate UL certificate CEE Rated CSA E
	RoHS Compliant
Hum And Noise Level	A
UL Recognized	No
Product Data	
Order product name	OPTANIUM ELE BALLAST (2) F32T8 347V

EAN/UPC - Product	781087142394
Order code	913701266202
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	913701266202
Net Weight (Piece)	350.000 g

Dimensional drawing



Product	A1	A2	B1	C1
OPTANIUM ELE BALLAST (2) F32T8 347V	9.5 in	8.90 in	1.3 in	1.0 in



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.