



NetKey® Patch Cord

NK6PC14YLY

Netkey copper patch cord, category 6, 14 ft., yellow UTP cable.

Specifications

Application	(1) Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), and 1000BASE-T (Gigabit Ethernet) (2) 155 Mb/s ATM, 622 Mb/s ATM, 1.2 Gb/s ATM (3) Token Ring 4/16 (4) Voice over internet protocol (VoIP)
Product Type	Patch Cord
Conductor Gauge (AWG)	24
Conductor Gauge (kcmil)	0.4
Performance Level	Category 5e
Conductor Type	Stranded
Cable Construction	U/UTP
Patch Cord Type	Unshielded
Connector 1 Type	Modular Plug
Connector 2 Type	Modular Plug
Overall Length (ft.)	14
Sub Brand	NetKey®
Nominal Cable Outside Diameter (In.)	0.21
Wiring Scheme	T568B
Maximum Operating Temperature (°F)	140
Minimum Operating Temperature (°F)	14
Maximum Storage Temperature (°F)	158
Boot Color	Clear
Color	Yellow
Flammability Rating	CM
Standards Met	Exceeds ANSI/TIA-568-C.2 Category 5e and ISO 11801 Class D channel requirements; Meets ANSI/TIA-568-C.2 and ISO 11801 Category 5e component requirements; Complies with ANSI/TIA-1096A; Meets IEC 60603-7; Supports IEEE 802.3af/802.3at; cULus Listed; UL 1863 and CAN/CSA-C22.2 (UL File E129886; CE Compliant; RoHS Compliant
IEC Variant	60603-7
PoE Compatibility	PoE, PoE+, PoE++
RapidID™ Enabled	No

Specifications (continued)

Part Features	100% performance tested, Patented tangle free latch, Slender strain relief boot, Identification and Variety of color and lengths available
---------------	--

Packaging Detail

UPC	07498305553
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.0351
Std. Ctn. Qty.	10
Std. Ctn. Volume (cf)	0.3514