

MODEL CF- 135W



Contact Ratings:

3 Amps at 125 VAC
1 Amp at 28 VDC
0.3 Amps at 125 VDC
0.1 Amps at 250 VDC

Dimensions:

Diameter 5.25 in (133 mm)
Height 2 in (51 mm)

Weight: 0.41 lbs. (0.19 kg)



The CF-135W is a fixed temperature only detector. The fixed temperature portion consists of a spring-loaded plunger retained by a fusible alloy that releases when the ceiling temperature reaches 135°F (57°C). When released, the plunger strikes a normally open set of contacts and holds them closed. Spacing on an uninterrupted ceiling is 40 ft (12.2 m). The CF-135 is identified by a black dot on its heat collector fin.