



## Copper Cable, Cat 6, 23 AWG, UTP, CMP, Black

PUP6C04BL-WLPZ

The TX6™ Cat 6 U/UTP copper cable is constructed of 23 AWG copper conductors with FEP/HDPE insulation. The copper conductors are twisted in pairs. All four pairs are surrounded by a PVC flame-retardant jacket. The black, plenum (CMP) cable is supplied 1,000 feet (305 meters) to an easy pay-out carton.

### Specifications

Note	Available in North America. COO USA
Environment	Indoor
Performance Level	Cat 6
Cable Construction	U/UTP
LP Rating	LP (0.5A)
Jacket Material	FEP
Nominal Cable Outside Diameter (In.)	0.205
Nominal Cable Outside Diameter (mm)	5.2
Sub Brand	Pan-Net®
Number of Pairs	4
Conductor Material	Copper
Conductor Type	Solid
Overall Length (m)	305
Conductor Gauge (AWG)	23
Insulation Material	Polyolefin
Color	Black
Overall Length (ft.)	1000
Packaging Type	Easy Payout Carton
Product Type	Copper Cable
Part Features	Copper Cable

**Packaging Detail**

UPC	61305686000
Std. Pkg. Qty.	1000
Std. Pkg. Volume (cf)	1.7315
Std. Ctn. Qty.	36000
Std. Ctn. Volume (cf)	62.3333