



## NetKey Cat 5e Punchdown Panel, Flat, 24-Port

NK5EPPG24Y

The NetKey® Flat Punchdown Keystone Patch Panel terminates 4-pair, 22–26 AWG, 100-ohm twisted pair cable. These Cat 5e patch panels mount to 19" and 23" racks and includes 24 ports. The RJ45 interface provides a quick plug and play connection to RJ45 patch cords. This punchdown patch panel is 1 RU, made of steel and is black.

### Specifications

Product Type	Punchdown
Termination Style	Punchdown
Patch Panel Style	Flat
Performance Level	Category 5e
Material	CRS
Wiring Scheme	T568A/T568B
Number of Ports	24
Module Type	RJ45
Number of Rack Units	1
Overall Width (In.)	19
Overall Width (mm)	482.6
Sub Brand	NetKey®
Overall Depth (In.)	1.17
Overall Depth (mm)	29.7
Overall Height (In.)	1.72
Overall Height (mm)	43.7
Identification Type	Adhesive Label
Color	Black
Standards Met	Exceeds ANSI/TIA-568-C.2 Category 5e and ISO 11801 Class D channel requirements at swept frequencies up to 100 MHz. Meets ANSI/TIA-568-C.2 and ISO 11801 Category 5e component requirements at swept frequencies up to 100 MHz. Complies with ANSI/TIA-1096A (formerly FCC Part 68), Meets IEC 60603-7, Supports IEEE 802.3af/802.3at and proposed 802.3bt type 3 and type 4 PoE applications, UL 1863 approved, RoHS Compliant
Maximum Operating Temperature (°C)	65
Maximum Operating Temperature (°F)	149
Minimum Operating Temperature (°C)	-10
Minimum Operating Temperature (°F)	-14

**Specifications (continued)**

Overall Length (In.)	1.17
Overall Length (mm)	29.7

**Packaging Detail**

UPC	07498305538
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.1619
Std. Ctn. Qty.	10
Std. Ctn. Volume (cf)	1.6189