SPDHMINI PATIO DOOR HEATER





STRENGTH AND SAFETY COMBINED

The SPDH model is the perfect example of a small electric baseboard heater that's a big hit in the world of heaters. The challenge: the patio door threshold. The accomplishment: traffic-resistant durability. At just 3 in. in both depth and height, the strength of the SPDH will surprise you. With its rounded front cover, this baseboard heater has a heat output of 150 W per linear foot.

- COMPACT AND ROBUST (3 IN. X 3 IN.)
 PERFECT UNDER PATIO DOORS AND LARGE WINDOWS
- DENSITY OF 150 W PER LINEAR FOOT
- BLANK SECTIONS AVAILABLE FOR A CONTINUOUS LOOK

COLOURS

- · standard: white, soft white
- Orora (optional): refer to www.stelpro.com/en-CA/Orora

FINISH

• epoxy-polyester powdercoat

MANUFACTURING

- 3 in. x 3 in. compact profile
- solid, 18-gauge steel cabinet and front that may be used as a step
- thermal protection with automatic reset
- full-length wireway
- pencil-proof openings of less than 1/4 in. (6.4 mm) prevent foreign objects from entering the unit

ELEMENT

 single tubular, stainless steel sheathed element with boxed aluminum fins for improved heat dissipation; the element is securely fastened at its centre, floating in nylon sleeves at each end, eliminating expansion and contraction noises

CONTROL

- wall thermostat (not included) the use of an electronic thermostat is strongly recommended
- built-in thermostat accessible without removing front grille, installed in the left junction box only (optional)
- low voltage relay kit installed in the left junction box only (optional)

INSTALLATION

- surface mounted
- wall or floor mounted with or without pedestal kit (optional)
- wiring compartment at both ends of unit
- blank sections (custom lengths) and accessories are available for a continuous look (optional)

WARRANTY

three years



IDEAL FOR:

below a patio door or a window, solarium



TECHNICAL SPECIFICATIONS						
150 W PER LINEAR FOOT		VOLTAGE LENGTH		NGTH	WEIGHT	
CODE	WATTS	VOLTS	MM	IN.	KG	LB
SPDH6031	300	120	600	23 5/8	2.7	6
SPDH6038	300	208	600	23 5/8	2.7	6
SPDH6032	300/225	240/208	600	23 5/8	2.7	6
	300	347	600	23 5/8	2.7	6
	300	600	600	23 5/8	2.7	6
SPDH9041	450	120	900	35 7/16	3.6	8
SPDH9048	450	208	900	35 7/16	3.6	8
SPDH9042	450/340	240/208	900	35 7/16	3.6	8
SPDH9043	450	347	900	35 7/16	3.6	8
	450	600	900	35 7/16	3.6	8
SPDH12061	600	120	1200	47 1/4	4.5	10
SPDH12068	600	208	1200	47 1/4	4.5	10
SPDH12062	600/450	240/208	1200	47 1/4	4.5	10
SPDH12063	600	347	1200	47 1/4	4.5	10
	600	600	1200	47 1/4	4.5	10
SPDH15071	750	120	1500	59 1/16	5.4	12
SPDH15078	750	208	1500	59 1/16	5.4	12
SPDH15072	750/560	240/208	1500	59 1/16	5.4	12
SPDH15073	750	347	1500	59 1/16	5.4	12
SPDH15076	750	600	1500	59 1/16	5.4	12
SPDH18091	900	120	1800	70 7/8	6.8	15
SPDH18098	900	208	1800	70 7/8	6.8	15
SPDH18092	900/675	240/208	1800	70 7/8	6.8	15
SPDH18093	900	347	1800	70 7/8	6.8	15
SPDH18096	900	600	1800	70 7/8	6.8	15
SPDH21101	1050	120	2100	82 11/16	8.2	18
SPDH21108	1050	208	2100	82 11/16	8.2	18
SPDH21102	1050/790	240/208	2100	82 11/16	8.2	18
SPDH21103	1050	347	2100	82 11/16	8.2	18
SPDH21106	1050	600	2100	82 11/16	8.2	18
SPDH24121	1200	120	2400	94 1/2	9.5	21
SPDH24128	1200	208	2400	94 1/2	9.5	21
SPDH24122	1200/900	240/208	2400	94 1/2	9.5	21
SPDH24123	1200	347	2400	94 1/2	9.5	21
SPDH24126	1200	600	2400	94 1/2	9.5	21
SPDH27138	1350	208	2700	106 5/16	10.4	23
SPDH27132	1350/1010	240/208	2700	106 5/16	10.4	23
SPDH27133	1350	347	2700	106 5/16	10.4	23
SPDH27136	1350	600	2700	106 5/16	10.4	23

Add W for white or SW for soft white (consult the optional colours chart or contact your Stelpro representative for all other colours). Models also available in 277 V and 480 V. --- not available

ACCESSORIES				
PRODUCT	DESCRIPTION			
SPDHT12*	built-in tamper-proof single pole thermostat			
SPDHRE153*	built-in electronic low voltage relay [15 A @ 120 V-347 V]			
SPDHRE156*	built-in electronic low voltage relay [6 A @ 600 V]			
SPDHRE153T*	built-in electronic low voltage relay c/w transformer 24 V [15 A @ 208 V-347 V]			
PK1*	pedestal kit (kit of two)			
SPDHJS*	joiner strip (2 in. – 51 mm)			
SPDHIC90*	inside corner (back measures 5 7/8 in. (149 mm) long on each side)			
SPDHOC90*	outside corner (back measures 5 7/8 in. (149 mm) long on each side)			
SPDHCB**	clean back (fully finished, no mounting holes or knockouts)			

Electronic relays can receive a PWM (pulsed width modulation) or digital (on/off) signal.

* Add W for white or SW for soft white.

* Factory installed

* Factory installation is strongly recommended.



TECHNICAL DRAWINGS

