

OB-430

HIGH PERFORMANCE RECESSED DOWNLIGHT



NAME:	
TYPE:	
DATE:	
NOTES:	

SPECIFICATIONS


LIGHT UNIT:	Aluminum Die cast with powder paint coat preventing discoloring and rusting.
WIRING:	Plenum rated cable used to connect light unit and junction box.
JUNCTION BOX:	Aluminum extrusion, with knockouts located at each end. Wiring compartment allows for (6) 14 gauge (AWG) insulated conductors. Connection to one (1) downstream unit is permitted within the junction box compartment. The compartment satisfies junction box volume requirements of CSA C22.2 No. 250.0/UL 1598
INSTALLATION:	Ideal for ceiling installations with no housing required. Steel spring clip for easy installation. Suitable for installation in t-grid and drop ceiling applications.
OPTICS:	COB (Chip on Board) LED technology uses light guided reflector to distribute light and optimize high level of delivered lumens. The regressed Gimbal design offers an anti-glare feature.
ELECTRICAL & PHASE CONTROL:	Easily connected to a 120V power supply via provided UL recognized driver. Optional 120-277V, 0-10V dimming driver available. Dimming down to 10% with most standard LED dimmers (see list of approved dimmers). Optional 90 CRI in 3" or 4", round or square, white finish only. Ambient operating temperature: -40°C (-40°F) to +40°C (+104°F). IC, WET Location and AIR-TIGHT rated. Phase Control: Forward Phase. Certifications: This product is ETL listed in USA & Canada, certified to UL standard 1598 and CSA standard C22.2 No. 250.0-08

CUTTING HOLE:	3.25" (82.6mm)
MOUNTING PLATE:	MP300 / AMP300 / MPHB250-450
BEAM ANGLE:	36°
GIMBAL ANGLE / HEAD ROTATION:	27° / 360°
COLOR TEMPERATURE:	3K - 4K all finishes
SELECTABLE COLOR TEMPERATURE:	No
CRI*:	80 - all finishes 90 - white only
LUMEN OUTPUT:	850 lumens - CRI80 / 700 lumens - CRI90
DIMMABLE:	Yes
WATTS:	10 Watts
LED LIFE:	50,000 hours
WARRANTY:	5 years
WIRE CABLE:	FT6 rated
DRIVER (SPECIAL ORDER):	120-277V, 0-10V Dimming


APPLICATIONS

The ORBIT series offers a high-performance LED (COB) recessed downlight with a pressure-fit spring clip application for an easy install. Whether it is a Remodel or New Construction installation, this unit is well suited for indoor / outdoor residential, hospitality, commercial and multifamily applications. It does not require a recessed housing for installation.

DIMENSIONS



ACCESSORIES



MOUNTING PLATE

Versatile square mounting plate allows for installation of all models of ndr lighting recessed lighting products. refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.



REMODEL VAPOUR BARRIER

The remodel vapour barrier unit may be used with all ndr lighting remodel housings. it is designed to prevent air leakage from your living space into the attic, or any insulated spaces.



ADJUSTABLE MOUNTING PLATE

Versatile adjustable mounting plate allows for installation of all models of ndr lighting recessed lighting products. refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.



GOOF RINGS

This goof ring is used when the ceiling hole is wider than the retrofit light unit being installed. refer to our goof ring compatibility chart to ensure the proper goof ring is selected.



UNIVERSAL MOUNTING PLATE WITH ADJUSTABLE HANGER BARS

This multi-size adjustable mounting plate allows for installation of all models of ndr lighting recessed lighting products. refer to our mounting plate compatibility chart to ensure the proper mounting plate is selected.



ORBIT MULTIPLATE

Our orbit line of led downlights is so amazing that you just cannot get enough of them! this orbit series accessory allows you to combine our 2" and 3" orbits into doubles or triples for an elegant, even brighter directional light source. just drop a couple of orbits in and they're installed faster than you think. a multiple look in seconds. "strength in numbers" has never been more relevant.

RATINGS



ORDERING GUIDE

ORBIT 430 Series

Series	Color Temperature	Finish	CRI
OB430-0510	3K 3000K/80CRI/10W	WH White	
	4K 4000K/80CRI/10W	BK Black	
		SC Satin Chrome	
	3K 3000K/10W	WH White	CRI90
	4K 4000K/10W	WH White	CRI90

Notes: Configure product using **BOLD** options: Ex: **OB430-0510-3K-WH**

SPECIAL ORDER: ORBIT 430 SERIES

Series	Multi-Volt 120-277V	Color Temperature	Finish	CRI
OBS43	277V	3K 3000K/80CRI/10W	WH White	
		4K 4000K/80CRI/10W	BK Black	
			SC Satin Chrome	
		3K 3000K/10W	WH White	CRI90
		4K 4000K/10W	WH White	CRI90

Notes: Configure product using **BOLD** options: Ex: **OBS43-277V-3K-WH**