Catalog Number: Date: Project:

OVERVIEW

The **WV 16** Series Wide View occupancy sensor is designed to mount in a corner and detect small motions up to 40 ft (12.19 m) away, and larger motions up to 70 ft (21.34 m) away. This makes it ideal for 30 ft x 30 ft (9.14 m x 9.14 m) classrooms or corridors up to 70 ft (21.34 m) long (for specific long narrow hallway applications, see **HW13** product data sheet). The enclosure's convenient tilting feature enables the sensor to be mounted at any height from 8 to 10 ft (2.44 to 3.05 m). When corner or wall mounting is not possible, the **WV BR** bracket accessory can be used to mount the **WV 16** to the ceiling. Additionally, the **WV 16** may be used in combination with other sensors to customize coverage for very large or irregularly shaped spaces. For rooms with obstructions, use the **WV PDT 16** Series sensor which adds Microphonics[™] detection.

FEATURES

- 100% Digital PIR Detection, Excellent RF Immunity
- 120° by 40 ft (12.19 m) Coverage for Small Motion
- Adjustable Time Delay
- Push-Button Programmable
- Convenient Test Mode
- No Field Calibration or Sensitivity Adjustments Required
- 100 hr Lamp Burn-in Timer

SPECIFICATIONS

Size: 3.0" H x 3.6" W x 1.75" D (7.62 cm x 9.14 cm x 4.45 cm)

Weight: 5 oz

Mounting: Directly to corner or to ceiling using **WV BR** bracket

Color: White

Operating Voltage: 12-24 VAC/VDC Current Draw: Standard, 4 mA

w/ R option, 16 mA

Rcmd Power Pack: **PP20**

ROHS compliant

AcuityControls.

Sensor Switch.

WV 16 Wide View Sensor





Warranty

Five-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Note: Actual performance may differ as a result of end-user environment and application.

Specifications subject to change without notice.




ORDERING INFORMATION

WV 16				Example: WV 16 R LT KIT
Series	Relay	Photocell	Temp / Humidity	Bracket Kit
WV 16 Wide View Sensor	[blank] None R Low Voltage Relay	[blank] None P Photocell	[blank] Standard LT Low Temp	[blank] Sensor Only KIT Sensor & WV BR Bracket

COVERAGE PATTERN

16 WIDE VIEW LENS

Small motion (e.g. hand movements) detection up to 40 ft (12.19 m).
Large motion (e.g. walking) detection up to 70 ft (21.34 m).
Designed for 8 to 10 ft (2.44 to 3.05 m) high mounting in room corner



WIRING (DO NOT WIRE HOT)

STANDARD WIRING

RED - Power Input (12-24 VAC/ VDC)

BLACK - Common

WHITE - Occupancy State (high VDC for occupied)

PHOTOCELL/DIMMING OPTIONS (P)

BLUE - Direct output to power pack for providing photocell control. Output is high VDC with occupancy & low light. For multi-level control, use two power packs and connect White wire to primary load and Blue to daylight load.

RELAY OPTION (R)

GRAY / BROWN - Connected during occupied state **VIOLET / BROWN** - Connected during unoccupied state

Note: Relay is energized during unoccupied state

