

FEATURES & SPECIFICATIONS

INTENDED USE — The industry's next generation in linear direct fluorescent products. This new compact, low-profile design offers our customers unique product features which improve the overall installation process and appearance while reducing labor cost, making it the most versatile solution for commercial, retail, manufacturing, warehouse, and cove and display applications.

ATTRIBUTES — Designed to accommodate a wide variety of T8 lamp lengths. Channel offers the gripper back feature which strengthens the overall construction and allows for the use of the new Z spring hanger (see back). Newly designed, patent-pending channel cover offers a secure fit design, allowing for easy access and quick attachment without pinching wires.

CONSTRUCTION — Constructed to comply with New York City electric code. Made in USA.

Compact designed channel and cover are formed from code-gauge cold-rolled steel. Innovative T8 two-lamp back plate offers compact design and additional socket protection. Locking lamp holder tracks bolsters strength of the overall strip construction while creating improved lamp stability. Design includes T8 socket, features rotating collar and enclosed contacts.

FINISH — High-gloss, baked white enamel finish (white standard). Five-stage iron-phosphate pretreatment ensures superior paint adhesion and rust resistance. Other channel paint finish options: black (MB), smoke gray (SMG) and galvanized (GALV).

OPTICAL — Reflector options include solid designs in both symmetric and asymmetric configurations. Consult factory for different-apertured versions.

ELECTRICAL SYSTEM — Thermally protected, resetting, Class P, HPF, non-PCB, UL listed.

Suitable for damp locations. AWN, TFN or THHN wire used throughout, rated for required temperatures.

INSTALLATION — Patented-pending "three-point" row connector locks channel together for straighter and faster row mounting; included as standard. Ideal for surface-mount or suspended.

LISTING — UL Listed, CUL Listed or CSA Certified to Canadian Standards.

WARRANTY — 1-year limited warranty. Complete warranty terms located at:

www.acuitybrands.com/support/warranty/terms-and-conditions

Note: Actual performance may differ as a result of end-user environment and application.


Specifications subject to change without notice.

ORDERING INFORMATION

Catalog Numbe		
Notes		Туре




Compact T8 Striplight



ZNY

Linear Lamps 1 or 2 Lamps




Specifications

Length: 18 (45.7), 24 (61.0) 36 (91.4), 48 (121.9)

72 (182.9) or 96 (243.8)

Width: 2-1/8 (5.4)
Depth: 1-1/2 (3.8)

All dimensions are inches (millimeters).





Example: Z 1 32 MVOLT GEB10IS

Series	Number of Lamps	Lamp Type	Voltage	Options
Z Compact strip¹ For tandem dou- ble-length unit, add prefix T. Example: TZ	1 2 Not included	17 17WT8 (24") 25 25WT8 (36") 32 32WT8 (48")	120 277 347 MVOLT Others available	GEB10IS T8 electronic ballast, ≤10% THD, instant start GEB10RS T8 electronic ballast, ≤ 10% THD, rapid star GLR Internal fast-blow fuse (add X for external) GMF Internal slow-blow fuse (add X for external) PLF_ Plug in wiring, specify number of branch circuits and hot wires (A-black, B-Red, C-Blue, AB or AC) (not for use with dedicated emergency circuits) EL55 Emergency battery pack (nominal 390-700 lumens); consult factory for additional battery packs ^{2,3} EL65 Emergency battery pack (nominal 725-1325 lumens) CSA CSA Certified NV I.B.E.W. union made, NYC code compliant

Accessories: Order as separate catalog number.								
SQ_ Swivel stem hanger (specify length in 2" increments up to 48") ZSPRG J2 Tong and T-grid hanger, for 15/16" T-grid (1 pair) Z8SMR48 Symmetric reflector, 4' white Z8ASR48 Asymmetric reflector, 3' white Z8ASR36 Asymmetric reflector, 3' white Z8SMR24 Symmetric reflector, 2' white	Z8ASR24 WGZ48 WGZ8SMR48 WGZ8ASR48 MS5ACF_ MS5AC_	Asymmetric reflector, 2' white 4' wireguard, white¹ 4' wireguard, white, for symmetric reflector¹ 4' wireguard, white, for asymmetric reflector¹ Adjustable aircraft cable system with power feed (specify length as 36, 72 or 108 inches)⁴ Adjustable aircraft cable system (specify 36, 72 or 108 inches)⁴						


For shortest lead times, configure products using **standard options** (shown in bold).

Notes

- 1. Order two 48" for 8' fixtures.
- 2. Specify voltage (available 120/277V).
- 3. Not available with CSA Certified.
- One cable per package.

INDUSTRIAL: FLUORESCENT Z-T8-NY

Z Compact Striplight



PHOTOMETRICS

Calculated using the zonal cavity method in accordance with IESNA LM41 procedure. Floor reflectances are 20%. Lamp configurations shown are typical. Full photometric data on these and other configurations available upon request.

