









Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

Trim Series	Dimensions	Aperture	Catalog No.	Housing/ Lamp Compatibility
 <p>Flushed Gimbal Ring</p>	 <p>Adjustment: PAR20 = 25° , ES20 = 35°</p>	<p>10 BRZ 10 BL 10 SC 10 WH</p>	<p>4" Adjustable Flush Gimbal Ring Trim - Bronze 4" Adjustable Flush Gimbal Ring Trim - Black 4" Adjustable Flush Gimbal Ring Trim - Satin Chrome 4" Adjustable Flush Gimbal Ring Trim - White</p>	<p>IC1P / TC1 / TC1 S / TC1R : 50W PAR20, 75W ES20 (Requires GU10WHIP) TC1RC W: 50W PAR20 APT1: 50W PAR20, 75W ES20 (Requires GU10WHIP)</p>
 <p>Mini Eyeball PAR16/ R16</p>	 <p>Adjustment: 35° Vertical</p>	<p>18 WH</p>	<p>4" Adjustable Mini Eyeball Trim - White</p>	<p>IC1 / IC1 W / IC1 S / IC1P / TC1 / TC1 S / TC1R: 60W PAR16, 40W R16 TC1RC W: 60W PAR16 APT1: 60W PAR16, 40W R16</p>
 <p>Flush Gimbal Ring</p>	 <p>Adjustment: 40° Vertical</p>	<p>440 BRZ 440 BL 440 SC 440 WH</p>	<p>4" Adjustable Flush Gimbal Ring Trim - Bronze 4" Adjustable Flush Gimbal Ring Trim - Black 4" Adjustable Flush Gimbal Ring Trim - Satin Chrome 4" Adjustable Flush Gimbal Ring Trim - White</p>	<p>IC1 / IC1 W / IC1 S: 35W MR16, 35W ES16 120V GU10 Base (Requires GU10WHIP) IC1P / TC1 / TC1 S / TC1RC W: 50W MR16, 50W MR16, 50W PAR16, 50W ES16 120V GU10 Base (Requires GU10WHIP) APT1: 50W MR16, 50W PAR16, 50W ES16 GU10 (Requires GU10WHIP)</p>
 <p>Adjustable Slot Aperture</p>	 <p>Adjustment: 40° Vertical</p>	<p>1-1/2" x 2-1/8" Oblong</p> <p>445 WH</p>	<p>4" Adjustable Slot Aperture Trim - White</p>	<p>IC44N / IC44N W / IC44N S / TC44 / TC44 V / TC44 S / TC44R: 50W MR16 TC47 / TC47 V: 75W MR16 APT44: 50W MR16</p>

Housing and trim can be ordered together or separate, but will always ship separately.