Basics Series[™] Surface Mount LED Fixtures Affordable and easy-to-install, 4" and 6" fixtures





Basics Series[™] Surface Mount LED Fixtures

Easiest to install LED fixture ever ... and so affordable!

There's never been an easier to install LED fixture than this one. The Juno® Basics Series™ Surface Mount LED fixture attaches directly to any standard junction box in two simple steps. No recessed housing required. Take it out of the box, and you're almost done.

Use it as a downlight or wall sconce. This super-thin fixture fits flush with any flat surface, mimicking the appearance of a recessed fixture. But without the need for a housing, installation time and fixture cost are kept to the bare minimum. This attractive, all-in-one design includes LED light engine, lens, and trim.



Big-time performance plus energy savings

The Juno surface-mount design offers performance and efficiency similar to typical LED recessed fixtures. The 4" 10-watt 4RLS Series is available in a 700 lumen version, while the 6" 6RLS is available in two lumen packages. The 14.5-watt 6RLS Series provides an impressive 1000 lumens, while the 10-watt 6RLS Series offers 750 lumens. These ultra-efficient fixtures provide energy savings of up to 85% compared to equivalent incandescent light sources. They are available in 2700K or 3000K CCTs with excellent 90+ CRI. Dimmable to 5%, they are compatible with many incandescent, magnetic low-voltage or electronic low-voltage dimmers.



Saves up to 85% in energy costs when compared to 65W incandescent light source

Juno® 4" and 6" Basics Series Surface Mount Fixtures

Product Specifications:



6RLS

- 4RLS Delivers 700 lumens at 10-watts with 90+ CRI
- Two 6RLS light engines available, 750 lumens from only 10-watts and 1000 lumens from only 14.5 watts, both with 90+ CRI
- 2700K or 3000K color temperature
- · Easy installation directly to junction box or existing 4" recessed housing via 4RLSRETROKIT or existing 5" and 6" recessed housings via 56RLSRETROKIT accessory
- Can be used as a downlight or a sconce
- Very low 1-1/8" profile (4RLS) and 1-1/4" profile (6RLS)
- · Beveled aluminum frame with white finish
- Dimmable with most standard incandescent, magnetic low voltage and electronic low voltage dimmers
- Five year limited warranty

Oualified Dimmers

voltage or electronic low voltage wall box dimmers. See specifications for a list of factory recommended dimmer models.

Installation

Junction Box Mounting

- Installs directly into industry standard junction boxes
- Compatible boxes include 3-½" and 4" octagon junction boxes (1-½" minimum depth), round mud rings with 2-3/4" mounting centers and 3" and 4" diameter non-metallic boxes
- · Quick-mount strap and spring securement system provides fast installation of fully assembled fixture to junction box
- Suitable for ceiling or wall mount
- Suitable for use within closet storage spaces when installed per NEC requirements

Recessed Housing Mounting - 4RLS

- Must use 4RLSRETROKIT accessory
- 4RLS is compatible with most 4" recessed incandescent housings with an inside diameter between 4" and 4-1/2" and a minimum height of 4"

Compatible Juno Housings - 4RLS

• Juno IC1 and TC1 Series

Recessed Housing Mounting - 6RLS

- Must use 56RLSRETROKIT accessory
- 6RLS is compatible with most 5" and 6" recessed incandescent housings with an inside diameter between 5" and 7" and a minimum height of 4"

Compatible Juno Housings - 6RLS

- Juno IC20, IC25, IC2, IC21, IC22, IC23, TC20 and TC2 Series
- VuLite V5IC, V6IC, V5TC, V6TC Series

Regulatory Listings & Standards



Approved for use in Wet Locations+ (indoor covered ceilings only)



Meets IECC air leakage requirements per ASTM E283



ENERGY STAR® Certified

UL and C-UL Classified



Can be used to comply with Title 24, Part 6, JA8 high efficacy LED light source requirements

RoHS Compliant

Compatible with incandescent, magnetic low

Catalog #	CI Codes	Description
4RLS G2 07LM 27K 90CRI 120 FRPC WH	251P66	4" Surface Mount Fixture, 700 lumens, 2700K
4RLS G2 07LM 30K 90CRI 120 FRPC WH	251P68	4" Surface Mount Fixture, 700 lumens, 3000K
4RLSRETROKIT	243V4V	Accessory kit for use when installing in existing 4" recessed housings
6RLS G2 07LM 27K 90CRI 120 FRPC WH	251P6A	6" Surface Mount Fixture, 750 lumens, 2700K
6RLS G2 07LM 30K 90CRI 120 FRPC WH	251P6F	6" Surface Mount Fixture, 750 lumens, 3000K
6RLS G2 10LM 27K 90CRI 120 FRPC WH	251P6J	6" Surface Mount Fixture, 1000 lumens, 2700K
6RLS G2 10LM 30K 90CRI 120 FRPC WH	251P6K	6" Surface Mount Fixture, 1000 lumens, 3000K
56RLSRETROKIT	243V66	Accessory kit for use when installing in existing 6" recessed housings

^{*}See installation guidelines provided with fixture for information on installing in wet location environments.

Juno® Basics Series™ Surface Mount LED Fixtures

Installation could not be easier ... or faster

No need for a recessed housing ... these surface-mount LED fixtures attach to a junction box in just two easy steps, dramatically reducing installation time and labor costs. And their ultra-low profile is ideal for applications where plenum space is severely limited. Alternatively, these compact fixtures can be quickly installed in new or existing, 4" or 5" or 6" recessed housings via a convenient accessory kit.











Installation is complete!



