






2

1

| REV | EC.NO. | DATE | DESCRIPTION | DFTR | CK. |
|-----|--------|------|-----------------|------|-----|
| A | | | INITIAL RELEASE | | |
| | | | | | |
| | | | | | |



SCALE 0.750

B

B

A

A

Size Face: 2x2 Module
 Size Backbody: 2x2 Module
 3rd Party Compliance: cETLus LISTED
 Ratings: 120 VAC
 Termination: Back Wire Only
 Misc: Copper Wire Only
 For Use With adorne System Only

| AANLM24, adorne Nightlight 2-Module | | | | | |
|---|-----------|---|-------|---------------------|--|
| MATERIAL | SEE NOTE | UNSPECIFIED TOL. FRAC. $\pm 1/64$ ANGLES ± 1.0 DEC $.0 \pm 0.02$ $.00 \pm 0.01$ $.000 \pm 0.001$ | | | |
| FINISH | SEE NOTE | | | MODEL NAME: AANLM24 | |
| DSGN BY: | 6/11/2015 | | | DWG.NO.: CD1187 | |
| DR.BY: | | SHT 1of1 | PROJ. | REV.: A | |
| CK.BY: | | SCALE: 1.000 | | | |
| NOTICE: Proprietary and confidential information of Pass & Seymour/Legrand Reproduction or disclosure prohibited under penalty of law. | | | | | |

2

1