

Series Spec Sheet

SWN

“NOAH” WET LOCATION ANTI VANDAL REMOTE

Single or double

6V, 12V & 24V lamps in LED & Quartz

The SWN series of wet location anti vandal remotes is designed to perform in extreme environments. The single or double lamp assemblies are completely protected from the elements within a fully gasketed polycarbonate housing. Available in 6 V, 12 V or 24 V models, utilizing quartz halogen or LED (bi-pin based) lamps.

FEATURES AND SPECIFICATIONS

- **Electrical and circuitry**

- 6 VDC, 12 VDC or 24 VDC
- Quartz halogen lamps - bi-pin based
- LED lamps - bi-pin based

- **Circuitry - CEREBRUM**

- This unit can be connected to Cerebrum’s smart battery unit. Please view the Cerebrum brochure for more details on this technology

- **Mechanical**

- Polycarbonate enclosure is fully gasketed around lens and canopy to prevent water infiltration
- Stainless steel tamper proof screws and bits
- Wet location
- Lamps are fully adjustable
- Fully gasketed housing
- Available in white and black
- Universal spider knockout pattern stamped into backplate for junction box mounting

- **Ambient Temperature**

- -35°C to +40°C

- **Approvals**

- CSA Certified to C22.2 #141-15
- CSA Certified type 2, 3, 3R, 4, 4X, 5, 12 or 12K
- CSA Certified to NSF 2
- IP66

- **Compliance**

- Meets requirements of ICES-005

OVERVIEW

Light source	LED or Quartz halogen
Input voltage (VDC)	6, 12, 24



For complete warranty details, please see our terms and conditions on our website.

TYPICAL SPECIFICATION



TYPICAL SPECIFICATION

Remote head shall be completely protected from the elements within a fully gasketed polycarbonate housing, be fully adjustable both tilt and swivel and have a universal spider knockout pattern stamped into back plate for junction box mounting. The SWN shall be 0 V, 0 W, 0 lumens. The MR16 LED's lamps shall be fully integrated in the molded shell to ensure extended life and maximum performance. The remote fixtures shall be certified to CSA 22.2 No.141-15, CSA Certified type 2, 3, 3R, 4, 4X, 5, 12, CSA Certified to NSF 2 and be ICES005 compliant. The remote unit shall be Stanpro model: SWN _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.

ORDERING GUIDE - LED

Series	Nbr of heads	Volts (VDC operational)	Watts (W)	Lamp type	Color
SWN	1 - Single head	06-24 - 6VDC to 24VDC operational	4W - 4 watts	LR - LED	BK - Black WH - White
	2 - Double head		5W - 5 watts	LA - LED	
		12-24 - 12VDC to 24VDC operational	6W - 6 watts	LA - LED	
			7W - 7 watts		
	1 - Single head	CER - Cerebrum driver	5W - 5 watts	LA - LED	
	2 - Double head	CER - Cerebrum driver	2.5W - 2.5 watts 5W - 5 watts		

ORDERING GUIDE - INCANDESCENT

Series	Nbr of heads	Volts (VDC)	Lamp type	Color
SWN	1 - Single head	06 - 6	See lamp selection chart	BK - Black
	2 - Double head	24 - 24		WH - White



INCANDESCENT LAMP SELECTION

	6 V	24 V
Quartz halogen	10WQ	12WQ

LEXAN GUARD

	Part number	Dimensions (in)
Wall Mount	PGD104	14 x 7.25 x 7.5

DIMENSIONS



LUMEN TABLE

Watts	Lumens
4W LR	388
5W LA	435
6W LA	507
7W LA	652

SPACING GUIDE

Mounting height	Spacing center to center (ft)			
	4WLR	5WLA	6WLA	7WLA
8 ft	76	81	94	108
10 ft	79	79	93	106
15 ft	66	62	82	96
20 ft	53	49	73	87

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.